

## Breadboard Enclosure System

These enclosure systems attach directly to our MB Series of Breadboards via the four counterbored mounting holes that are provided on all boards in this series. These enclosures are ideal for protecting delicate instruments that are constructed on the MB

Series of Breadboards. All stock enclosure systems have an internal height of 12" (30 cm). For light-sensitive instruments, we offer enclosures with black hardboard sides. The enclosures are shipped flat and can typically be assembled in less than 30 minutes. The only tool necessary for assembly is a hex key wrench.

- Enclosure Ships Unassembled
- Lightweight Black Hardboard Panels for Light-Sensitive Applications
- Complete Line of Accessories Allows Field Building of Custom Enclosures
- Mounts Directly to Our MB Series of Breadboards Featured on Page 3.
- Custom Sizes Available Upon Request



Shown with Plexiglass  
(Breadboard Sold Separately)



Breadboard Not Included (See Page 3)

## Enclosure with Door Assembly

Our Enclosure Door Assembly provides convenient access to optical assemblies within the structure. Panel-mounted handles and a bottom-located slide track make for smooth operation. This feature is currently only available for the enclosures designed for use with our MB1824 and MB4560/M breadboards.



XE25C5D  
(Breadboard Sold Separately)

## Enclosure with Black Hardboard

Our enclosures with black hardboard can be used in light-sensitive applications and when it is necessary to eliminate stray light from exiting a setup. Versions with hardboard can be ordered with or without a sliding door for access to the setup.

### 1/4"-20 Breadboard Enclosure Systems, 12" High (Measured Internally)

ITEM #	\$*	£*	€*	RMB*	COMPATIBLE BREADBOARD	INTERNAL DIMENSIONS	DESCRIPTION
XE25C1	\$ 152.00	£ 109.44	€ 132.24	¥ 1,211.44	MB1218	9" x 15"	Breadboard Enclosure for MB1218, Black Hardboard
XE25C3	\$ 168.00	£ 120.96	€ 146.16	¥ 1,338.96	MB1224	9" x 21"	Breadboard Enclosure for MB1224, Black Hardboard
XE25C5	\$ 178.00	£ 128.16	€ 154.86	¥ 1,418.66	MB1824	15" x 21"	Breadboard Enclosure for MB1824, Black Hardboard
XE25C5D	\$ 199.00	£ 143.28	€ 173.13	¥ 1,586.03	MB1824	15" x 21"	Breadboard Enclosure for MB1824, Black Hardboard with Door
XE25C6	\$ 212.00	£ 152.64	€ 184.44	¥ 1,689.64	MB1824	15" x 21"	Breadboard Enclosure for MB1824, Plexiglass
XE25C6D	\$ 230.00	£ 165.60	€ 200.10	¥ 1,833.10	MB1824	15" x 21"	Breadboard Enclosure for MB1824, Plexiglass with Door

\*Price does not include breadboard. See page 3.

### M6 Breadboard Enclosure Systems, 300 mm High (Measured Internally)

ITEM #	\$*	£*	€*	RMB*	COMPATIBLE BREADBOARD	INTERNAL DIMENSIONS	DESCRIPTION
XE25C1/M	\$ 152.00	£ 109.44	€ 132.24	¥ 1,211.44	MB3045/M	225 mm x 375 mm	Breadboard Enclosure for MB3045/M, Black Hardboard
XE25C3/M	\$ 168.00	£ 120.96	€ 146.16	¥ 1,338.96	MB3060/M	225 mm x 525 mm	Breadboard Enclosure for MB3060/M, Black Hardboard
XE25C5/M	\$ 178.00	£ 128.16	€ 154.86	¥ 1,418.66	MB4560/M	375 mm x 525 mm	Breadboard Enclosure for MB4560/M, Black Hardboard
XE25C5D/M	\$ 199.00	£ 143.28	€ 173.13	¥ 1,586.03	MB4560/M	375 mm x 525 mm	Breadboard Enclosure for MB4560/M, Black Hardboard with Door
XE25C6/M	\$ 212.00	£ 152.64	€ 184.44	¥ 1,689.64	MB4560/M	375 mm x 525 mm	Breadboard Enclosure for MB4560/M, Plexiglass
XE25C6D/M	\$ 230.00	£ 165.60	€ 200.10	¥ 1,833.10	MB4560/M	375 mm x 525 mm	Breadboard Enclosure for MB4560/M, Plexiglass with Door

\*Price does not include breadboard. See page 3.